Model 158

Specifications

Model 158 is a seven tube superheterodyne designed for operation from A. C. electric circuits. The intermediate frequency used is 181.5 KC.

Tubes And Voltage Limits

The following are the voltages measured with the receiver in operating condition, but with no signal to the antenna circuit. Use a high resistance D. C. Voltmeter (1000 ohms per volt, or more) for all but filament voltages. In measuring filament or heater voltages use

a low range A. C. meter. The voltage limits are + or - 10% of values given in the following table.

Line voltage-117.5 (235 for 220 volt receivers).

Plate voltage measured from plate contact to cathode contact.

Screen grid voltage measured from screen

grid contact to cathode contact. Suppressor grid voltage measured from sup-

pressor grid contact to cathode contact. Bias voltage measured from cathode con-

'act to chassis.

Tube Position	Plate	Screen Grid	Voltages Supp. Grid	Bias	FIL
68 R. F. Amplifier	270	85	0	0	2.5
57 Oscillating Detector	270	80	0	6.0	2.5
58 I. F. Amplifier	275	80	0	4.0	2.5
56 Detector	0				2.5
56 A. F. Amplifler	40			1.6	2.5
42 Output	245	250		22.0	6.3
80 Rectifier	350				4.8

